


Tutorial Panels Uno **Volta**

UV-102

Tutorial Panel for Connection of Light Supply with Discharge Lamps

The UV-102 tutorial panel is an extension panel of UV-101 and is used to practice and make experiments with connecting light sources with halogen bulbs and lamps. This panel is supplied with 230 V / 50 Hz voltage from the power supply.



Parts used

Sleeves E27


Choke

Electronic ballast

Halogen bulb with socket E27, 50W

Pressure sodium lamp E27, 70W

Mercury lamp with a socket E27, 50W



Examples of connection

- Connection of a fluorescent lamp with a halogen bulb
- Connection of a fluorescent lamp with a classic bulb
- Connecting of a lamp, assembling of a circuit with individual elements (choke, ballast)
- Possibility to compare the luminosity and efficiency of each individual light source between each other.
- The UV-101 panel can be also used for a similar comparison.

Příslušenství:

- Napájecí šňůra 230V
- Návod k obsluze

Doporučené příslušenství:

- Taška pro uskladnění panelu a jeho převoz
- Propojovací bezpečnostní kabely
- Náhradní žárovky a zářivky
- Soubor úloh

Contacts

Diametral Plc

Vaclava Spacka 1759

193 00 Prague 9 - Horní Počernice European Union - Czech republic

+420 222 360 423 variolab@diametral.cz

All rights reserved Diametral Plc

© 8/2019 ver. 1.0